#### PRODUCT DATASHEET

## **APPLICATIONS**

- Aerospace analysis
- Automotive safety
- Biomechanics
- Component testing
- Dummy calibration
- · Static bench top testing
- Vibration testing

# SLICE PRO LAB

# Stationary, Laboratory Data Acquisition System





SLICE PRO LAB SIM (left) is a modular, standalone data recorder with 9 or 18 fully-programmable sensor input channels.

SLICE PRO LAB TOM (right) is a modular, standalone airbag timer with 4 independent squib fire channels and 8 digital output channels.

#### **Features**

- A complete solution with programmable sensor interface, adjustable filters, 16-bit ADC and Ethernet communication
- Two intuitive DTS software options: SLICEWare and DataPRO
- SLICE PRO LAB SIM includes 9 or 18 fully-programmable sensor input channels with isolated excitation
- SLICE PRO LAB TOM includes 4 isolated squib fire channels and 8 separate digital outputs for controlling other systems requiring timed outputs—0.1 msec resolution
- User-selectable sampling rates up to 1M sps/channel
- · Data bandwidth options up to 200 kHz
- Record from milliseconds to hours. Data stored directly to 16 GB non-volatile flash memory.
- Supports a variety of external sensors, including full and half-bridge sensors, strain gages, IEPE, voltage input, thermocouples, etc.
- Meets NHTSA, FAA, ISO 6487 and SAE J211 data acquisition requirements


The SLICE PRO LAB system from DTS features the same electronics and flexibility as the crash-hardened SLICE PRO modules, but in laboratory enclosures. Ideal for a variety of static tests, modules can be configured into any combination in the SLICE PRO LAB Rack. Each rack holds up to four modules and includes an Ethernet Controller, plus the system is compatible with other DTS hardware.



The SLICE PRO LAB Rack is a standard 19-inch x 3U and holds up to 4 modules. Racks can be daisy-chained to support high channel count tests.

#### **Software**

DTS offers two great software options for all SLICE products that allow users to simply enter sensor information and sampling parameters and the software automatically sets-up the hardware. SLICEWare offers fast, easy tools for storing sensor information and performing data collection. DataPRO offers a full-featured database and user interface for tracking sensor information, creating test objects and test setups, performing diagnostic routines and running tests. Both software options feature the most advanced self-diagnostics available, plus support for EQX and numerous data exchange file formats.





#### **PRODUCTS**

Diversified Technical Systems designs and manufactures data acquisition systems, sensors, and software for beginning and advanced test professionals.



#### COMPATABILITY

Already have DTS equipment?

Did you know SLICE PRO LAB is compatible with SLICE PRO, TDAS PRO, TDAS PRO LAB and TDAS G5 hardware using DataPRO software.

#### **SERVICES**

24/7 Worldwide Tech Support ISO 17025 (A2LA) Calibration On-site Calibration & Training **Application Consulting** Software Integration **OEM/Embedded Applications** 

#### **TECH CENTERS**

Michigan, United States **United Kingdom** France

Japan Asia Pacific

#### **HEADQUARTERS**

Seal Beach, California USA

#### **CONTACT US**

Phone: +1 562 493 0158 Email: sales@dtsweb.com

### **Specifications**

#### [Please See SLICE PRO Datasheets for Additional Details]

Module Size: 13.2 x 9.7 x 10.9 cm (5.2 x 3.8 x 4.3")

Module Weight: LAB SIM 0.8 kg (1.80 lb)

LAB TOM 0.8 kg (1.80 lb)

Fits in SLICE PRO LAB Ethernet Rack Compatibility: 4 Module Rack Size: 48.3 x 17.8 cm x 3U high (19" x 7" x 3U) 4 Module Rack Weight: 4.2 kg (9.3 lb) includes Ethernet Controller

**POWER** 

Supply Voltage (rack): 15 VDC nominal; 9-15 V range

(LAB systems do not contain internal batteries) 40 W via the SLICE PRO LAB Ethernet Rack

Power (Maximum): Power Control: Push button, not impact critical

Protection: Reverse current, ESD

**ENVIRONMENTAL** 

0-50°C (32-122°F) Operating Temp:

#### SLICE PRO LAB SENSOR INPUT MODULE (SIM)

Bridge or Voltage Sensor Interface

No. of Channels: 9 or 18

Type: Differential Instrumentation Amplifier Sensor Connectors: LEMO 1B, 2B or Tajimi rectangular Common Mode Range: ±3.5 V, centered 2.5 V above ground Differential Input Range: ±2.5 V, centered 2.5 V above ground

Bandwidth: DC to 200 kHz Gain Range: 1 to 12.000

Excitation Voltage: Off, 2.0, 5.0, 7.5 and 10.0 V selected in software Bridge Support: 3k ohm half-bridge completion. 120 or 350 ohm

3/4 bridge completion for strain gages, etc. Shunt Check: Emulation method, automatically calculated Maxim Integrated (Dallas) "1-wire" silicon serial

IEPE Sensor Interface (if so equipped)

0.5 to 23.5 V Input Range:

4.0 mA constant current with 25 V source. Excitation: Contact DTS for other options if needed. Works with EID or "TEDS" equipped sensors Sensor ID:

Anti-Alias Filters (AAF)

Sensor ID:

Fixed Low Pass: 8-pole fixed Butterworth with factory configured

maximum bandwidth.

Options: 4.0 kHz, 100 kHz, 200 kHz

Adjustable Low Pass: 5-pole Butterworth set under software control:

50 to 45 kHz (bypassed for maximum

bandwidth)

**Custom Options:** Contact DTS for any special requirements Overall Response: System response complies with SAE J211/

ISO 6487 recommended practices

**Analog to Digital Conversion** 

16-bit SAR (Successive Approximation Type:

Register) ADC, one per channel, simultaneous

sample of all channels

**Start and Trigger Options** 

Level Trigger: Positive or negative level on any active sensor

channel (first level crossing of any programmed

sensor triggers system)

Software Trigger: Data collection may be started or triggered via

**Data Recording** 

Recorder, circular buffer and multiple test Modes:

modes available

16 GB non-volatile flash per module Memory: Sample Rate: User-programmable from 100 sps to 1M sps Maximum 1M sps/ch with 9 channels used or 500k sps/ch with18 channels used per SIM

PC INTERFACE

SLICE PRO Ethernet Controller (included with Rack)

Description: Interface for start, status, event, power and 10/100 Ethernet communication signals System Capability: Each Controller supports up to 72 channels and

provides interconnection compatibility with additional SLICE PRO systems, TDAS PRO & TDAS G5 systems. 100s of channels can be

combined in one setup.

COM: LEMO 2B 19-pin, Power: LEMO 2B 4-pin Connectors:

Note: Ethernet Controller "COM" ports are 100% compatible with TDAS PRO and G5 COM ports. SLICE PRO LAB TIMED OUTPUT MODULE (TOM)

**Squib Fire Channels** 

Number: 4 per module

**Energy Delivery:** Capacitive discharge, constant current

Source Voltage:

Constant Current Output: 1.0-4.0 A software adjustable in 0.1 A

increments.

**Timing Control** 

Method: Delay for each output channel can be

independently programmed via software

Delay Range: 0-99 seconds after trigger input Squib Duration: 0.2-25.5 msec or continuous Digital Output Duration: 0.2-1.6 msec or continuous

Resolution: 0.1 msec

**Event Input** 

Each Module: Standard contact closure input, galvanically

and optically isolated to 1 kV EMI, RFI and ESD protection False Trigger:

Event input may be connected in parallel across Multiple Modules:

several modules

**Output Waveform Recording** 

General: Two measurements/ch (8 total per module):

1) current waveform

2) initiation signal/voltage waveform Method: 16-bit SAR (Successive Approximation

Register) ADC, one per channel, simultaneous

sample of all channels.

Sampling Capability: Up to 500k sps with adjustable anti-alias filter

automatically set under software control 16 GB non-volatile flash per module

Memory Type: **Digital Output Channels** 

General: 8 outputs available on a single connector Output Type: Compatible with devices requiring isolated

contact closure and/or CMOS/TTL-compatible levels (0-5 V). Logic polarity is software

programmable.

SOFTWARE

SLICEWare, DataPRO, API Control:

\*NOTE: Timed Output Module (TOM) requires

DataPRO software

Operating Systems: Windows® Vista/7/8/10 (32- and 64-bit)



SLICE PRO LAB fits into a standard 19 inch rack configuration.

Sleek handles make it quick and easy to reconfigure systems.



A portable bench-top enclosure is also available for a single rack system.



Specifications subject to change without notice. © Diversified Technical Systems, Inc.